



```

XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters

```

Cable Length(L): 01~99Meters



*  Important Dimensions To Check
 * Waterproof Rate: IP67
 * Housing: Nylon+GF, Black
 * Male Pin: Copper Alloy, Gold Plated
 * Cable: UL2464 24#*5C+D+Al/My,UV, PVC Jacket, Black,
 OD=5.0mm

△B* Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm

△B* Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm

△C* Cable Length Tolerance: 1M:±40mm
2M~5M:±60mm
6M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



5	Green	綠
4	White	白
3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

UNIT: mm		
TOLERANCE		
$\pm 0.5 \text{ mm}$		

TITLE		Standard	
Cable Screw 5Pin M Conn M Pin			
SCALE	3:2	SIZE	A4
		SHEET	1 OF 1
REV.	D	WC-REV.	A.1
			QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Ruru	2017-09-27
DWG NO	CHECKED BY	DATE
BD-05PMMM-SL7AXX	Rita	2017-09-27
CUSTOMER	APPROVED BY	DATE
ALTW	Max	2017-09-27

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-05PMMM-SL7A02](#) [BD-05PMMM-SL7A10](#) [BD-05PMMM-SL7A01](#) [BD-05PMMM-SL7A05](#)