


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1190179~182	2011/08/24	Jiang Jun Hua	Change SR View
C	LEN1620090~093	2016/01/08	Ruru	Change Logo



BD-06AFFM-SR7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
:
99:99Meters

Cable Length(L):01~99Meters

- Note:
- * @@Important Dimensions To Check.
 - * Waterproof Rate:IP67
 - * Housing: Nylon+GF,Black
 - * Pin: Copper Alloy,Gold Plated
 - * Cable: UL2464 24AWG*6C+Drain+Al/My,Black PVC Jacket UV Resistant, OD=5.8
 - * Cable Length Tolerance:01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

A	UNIT:mm				TITLE			Amphenol LTW 安費諾亮泰企業股份有限公司			ITEM NO			DRAWN BY			DATE			BY Amphenol LTW.																			
	TOLERANCE ±0.5 mm				Standard, Cable Screw 6Pin F Conn F Pin						DWG NO			CHECKED BY			DATE																						
					SCALE						SHEET			BD-06AFFM-SR7AXX			Rita				2016/01/08																		
					REV.		SIZE				QC			Inspection Item			CUSTOMER				APPROVED BY			DATE															
C		A4		②②			:Inspection Item			ALTW			Lisa			2016/01/08																							
1					2					3					4					5					6					7					8 FMW0702-01-01A2				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-06AFFM-SR7A05](#) [BD-06AFFM-SR7A01](#) [BD-06AFFM-SR7A10](#) [BD-06AFFM-SR7A02](#)