




```


XX:01~99Meter
01:01Meter
02:02Meters

```

99:99Meters
n(L):01~99Meters



Pin Assignments Front View



Recommended Panel Cut-Out

6	White	白
5	Red	紅
4	Orange	橙
3	Yellow	黃
2	Green	綠
1	Blue	藍
Conn.	Wire Color	
	Pin Out	

- *  Important Dimensions To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24*6C+D+Al/My,UV, PVC Jacket, Black, OD=5.8mm
- *  Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- *  Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- *  Cable Length Tolerance: 1M:±40mm
2M~5M:±60mm
6M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT: mm	
TOLERANCE	
$\pm 0.5 \text{ mm}$	

TITLE		Standard	
Cable Screw 6Pin M Conn M Pin			
SCALE	3:2	SIZE	A4
REV.	D	SHEET	1 OF 1
	WC-REV.	A.1	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Ruru	2017-09-28
DWG NO	CHECKED BY	DATE
BD-06PMMM-SL7AXX	Rita	2017-09-28
CUSTOMER	APPROVED BY	DATE
ALTW	Max	2017-09-28

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-06PMMM-SL7A10](#) [BD-06PMMM-SL7A05](#) [BD-06PMMM-SL7A02](#) [BD-06PMMM-SL7A01](#)