




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1590373~76	2015/09/11	Ruru	Change Logo & Note
C	LE31630175~78	2016/02/24	Ruru	Update Bubble Ball



Pin Assignments
Front View

Conn. I	Wire Color
7	White
6	Green
5	Brown
4	Red
3	Yellow
2	Orange
1	Blue
Pin Out	

XX:01~99Meter
01:01Meter
02:02Meters
...
99:99Meters
Cable Length(L):01~99Meters

Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP67
- * Connector: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24AWG*7C+Drain+Al/My, (UV Resistant) OD=5.8mm, Black
- * Cable Length Tolerance: 01M: ± 40 mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
± 0.5 mm		3:2		BD-07BMMM-L180 to Cable		BD-07BMMM-LL7AXX		Ruru		2016-02-24	
C		A.1		SHEET 1 OF 1		ALTW		Rita		2016-02-24	
				WC-REV.				Lion		2016-02-24	

Amphenol LTW

安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-07BMMM-LL7A02](#) [BD-07BMMM-LL7A10](#) [BD-07BMMM-LL7A01](#) [BD-07BMMM-LL7A05](#)