

Technical drawing of the BSB-04BFFM-SL7000 cable assembly. The drawing shows a side view and a top view.

**Side View Dimensions:**

- Total length: 7000 L(mm)
- Cable diameter: Ø5.5
- Connector length: 37.8
- Outer diameter: Ø19.0

**Labels:**

- Cable 2
- BSB-04BFFM-SL7000
- 1

**Top View:**

- Conn.



BSB-04BFFM-SL7AXX

XX:01~99Meter

01:01 Meter

02:02Meters


- 
- 
- 
- 

99:99Meters

Cable Length(L):01~99Meters

Note:


- \* QC Important Dimension To Check.
- \* Waterproof Rate:IP67.
- \* Housing:Nylon+GF,Black.
- \* Female Pin:Copper Alloy,Gold Plated.
- \* Screw Nut:Copper Alloy,Nickel Plated.
- \* Shell:Copper Alloy,Nickel Plated.
- \* O-Ring:EPDM,Black.
- \* Cable:UL2464 20AWG\*4C+Drain+Al/My,Black,  
PVC Jacket,UV Resistant,OD=5.5mm.
- \* Cable Length Tolerance: 01M:±40mm  
02M~05M:±60mm  
06M~10M:±100mm  
11M~30M:±200mm  
31M~99M:±500mm



### Pin Assignments

#### Front View

Shield	Drain	地線
4	White	白
3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin	Out



UNIT:mm	
TOLERANCE	
$\pm 0.5$ mm	

TITLE		Standard	
Cable Screw 04P F Conn F Pin			
SCALE	Free	SHEET	1 OF 1
REV.	A	SIZE	A4
		QC : Inspection Item	

# Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2010/01/12
DWG NO BSB-04BFFM-SL7AXX	CHECKED BY Rita	DATE 2010/01/12
CUSTOMER ALTW	APPROVED BY Lion	DATE 2010/01/12

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BSB-04BFFM-SL7A01](#)