






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-0C0629~633	2010/11/26	Ivan	Change View.
C	LEN1140003~007	2011/03/28	Jiang Jun Hua	Change SR View.
D	LEN15C0404~408	2015/12/10	Ruru	Change Logo



BU-10AFFM-SR7AXX


XX:01~99Meter
01:01Meter
02:02Meters
:
:
:
99:99Meters

Cable Lenght(L):01~99Meters



Pin Assignments
Front View

Orange	橘	10
Black	黑	9
Red	紅	8
Pink	粉紅	7
Gray	灰	6
Yellow	黃	5
Green	綠	4
White	白	3
Blue	藍	2
Brown	棕	1
Wire Color		Conn.
Pin Out		



Note:

- * @@ Important Dimension.
- * Waterproof Rate: IP67.
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Cable: UL2464 26AWG*10C+Drain+Al/My, PVC Jacket, UV Resistant, OD=6.0mm, Black.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm	
TOLERANCE	±0.5 mm

TITLE		Standard	
Cable Screw 10Pin F Conn. F Pin			
SCALE		Free	SHEET 1 OF 1
REV.	D	SIZE	A4
QC :Inspection Item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ALTW	Lisa	2015/12/10

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-10AFFM-SR7A06](#) [BU-10AFFM-SR7A03](#)