

1	2	3	4	5	6	7	8	
				REV. B	ECN NO. LEN-0C0641~645	DATE 2010/11/26	SIGN Ivan	DESCRIPTION Change View
				C	LEN15C0415~420	2015/12/10	Ruru	Change Logo

BU-10BFFM-SL7000
Color: Black

BU-10BFFM-SL7AXX

XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

ALTW
DCC. DEPT.
CONFIDENTIAL
2015.12.24
ISSUED

ALTW
CONFIDENTIAL
2015.12.10
R&D DEPT.

Pin Assignments
Front View

10	Orange	橘
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

Note:

- * @@Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 26AWG*10C+Drain+Al/My
PVC Jacket UV Resistant OD=6.0mm, Black
- * Cable Length Tolerance:01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE	Standard
TOLERANCE		Cable Screw 10Pin F Conn. F Pin	
±0.5 mm		SCALE Free	SHEET 1 OF 1
		REV. C	SIZE A4
		QC :Inspection Item	

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2015/12/10
DWG NO BU-10BFFM-SL7AXX	CHECKED BY Rita	DATE 2015/12/10
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015/12/10

1

2

3

4

5

6

7

8 FMW10702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-10BFFM-SL7A10](#) [BU-10BFFM-SL7A01](#) [BU-10BFFM-SL7A05](#) [BU-10BFFM-SL7A02](#)