





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0405~408	2008/09/22	Shin	Add Note
C	LEN1590279~282	2015/09/03	Vicky	Update Logo & Note
D	LEN1650415~418	2016/05/13	Ruru	Modify Logo Position



Note:

- * QC Important Dimensions To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 26#*10C+D+Al/My, UV, PVC Jacket, Black, OD=6.0mm

$\triangle B^*$ Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm

$\triangle B^*$ Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm

$\triangle C^*$ Cable Length Tolerance: 1M:±40mm
2M~5M:±60mm
6M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

UNIT:mm		TITLE	Standard
TOLERANCE	±0.5 mm		Cable Lock 10Pin M Conn M Pin
SCALE	3:2	SIZE	A4
REV.	D	WC-REV.	A.1
		QC	Inspection item

ITEM NO	DRAWN BY	DATE
DWG NO	Ruru	2016-05-13
CUSTOMER	CHECKED BY	DATE
ALTW	Rita	2016-05-13
	APPROVED BY	DATE
	Lisa	2016-05-13

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-10PMMM-LL7A03](#)