




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1590399~402	2015/09/11	Ruru	Change Logo & Note
C	LE315C0398~401	2015/12/16	Ruru	Modify Ball-marker



Pin Assignments
Front View前視圖

12	Light Green	淺綠
11	Purple	紫
10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn	Wire Color	
Pin Out		

BU-12BMMM-LL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
:
99:99Meters

Cable Length(L):01~99

- Note:
- * @C Important Dimension.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy,Gold Plated
 - * Cable: UL2464 26AWG*12C+Drain+Al/My, UV Resistant, OD=6.0mm, Black
 - * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm	
TOLERANCE	±0.5mm

TITLE Lock Type Cable Assembly-180° 12Pin Male Connector Male Pin(2A)		
SCALE Free	SHEET 1 OF 1	
REV. C	SIZE A4	@C :Inspection Item

Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO	DRAWN BY Ruru	DATE 2015/12/16
		DWG NO BU-12BMMM-LL7AXX	CHECKED BY Rita	DATE 2015/12/16
		CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015/12/16

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-12BMMM-LL7A10](#) [BU-12BMMM-LL7A02](#) [BU-12BMMM-LL7A01](#) [BU-12BMMM-LL7A05](#)