







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
D	LEN1330121	2013/03/28	Yulong	Change The Dimension
E	LEN1590305	2015/09/02	Vicky	Update Logo
F	CI90269	2019/02/26	Ruru	Modify Note



Pin Assignments
Front View



Recommended Panel Cut-out



- Note: Important Dimension To Check
- * Waterproof Rate: IP67, Unmated
 - * Housing: Thermoplastic, Black
 - * Pin: Copper Alloy, Gold Plated
 - * Nut: Thermoplastic, Black
 - * Gasket: Rubber, Black
- * Use With Waterproof Cap Or Dust Cap
Panel Thickness Max: 3.0mm
- * Use Without Waterproof Cap Or Dust Cap
Panel Thickness Max: 4.0mm
- * Gasket and Nut are packed separately in PE bags.

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
.X ±0.25		.XX ±0.1		Standard		BU-12PMMS-SC7001		Ruru		2019-02-26	
.XXX ±0.05		ANGLES ±1°		Panel Screw 12Pin M Conn M Pin		DWG NO		CHECKED BY		DATE	
SCALE 2:1		SIZE A4		SHEET 1 OF 1		BU-12PMMS-SC7001		Rita		2019-02-26	
REV. F		WC-REV. B.3		QC: Inspection item		CUSTOMER		APPROVED BY		DATE	
						ALTW		Max		2019-02-26	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-12PMMS-SC7001](#)