



^a under operating conditions >10⁸ Ohm
^a designed according pollution degree 2, can be used under pollution degree 3 if the rules according IEC 60664-1 are fulfilled

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
 All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties ("Beschaffheitsgarantie" or "Haltbarkeitsgarantie").

Gewicht (errechnet) / Calc WT :				g		Zul. Abw./Tolerances :  DIN / ISO 13715		Maßstab / Scale :		2:1		A3				
 Prüfmaß / Testdimension				Teileindex Partindexnumber				Material: Oberfläche:								
				2013	Datum/ Date	Name		female cable connector for cable diameters 8-10,5								
				Gez.	17.05.	Carle										
				Drawn												
				Gepr.												
				Checked												
02	201300837	04.12.13	IM	Amphenol-Tuchel Electronics GmbH				M	C091 11DXXX 002 4 U						Blatt/ Sheet 1	
01	201300382	02.07.13	CM												1 Bl.	
Index	Änderung/ Description	Datum/ Date	Name					Ers. f. / Replacement for :								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C09111D0120024U](#)