


4	White	白
3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

CB-04AFMM-LL7AXX

```
XX : 01~99Meters  
01 : 01Meter  
02 : 02Meters  
:  
:  
:  
99 : 99Meters
```

Cable Length(L):01~99Meters

Note:

- *  Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Lock Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 20AWG*4C+Drain+Al/My,
Black,PVC Jacket,UV Resistant,OD=5.5
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT: mm		
TOLERANCE		
$\pm 0.5 \text{ mm}$		

TITLE		Middle Cable Lock 4Pin F Conn M Pin	
SCALE	1:1	SIZE	A4
REV.	C	SHEET	1 OF 1
	WC-REV.	A.1	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2014-07-25
DWG NO CB-04AFMM-LL7AXX	CHECKED BY Sam	DATE 2014-07-25
CUSTOMER ALTW	APPROVED BY Rita	DATE 2014-07-25

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1CB-04AFMM-LL7A01](#)