





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0155~58	2008/09/25	Shin	Add Note
C	LEN1630478~481	2016/03/14	Ruru	Change Logo & Note



Recommended
Panel Cut-Out



Pin Assignments
Front View



CB-04PMFM-LL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters

Cable Length(L):01~99Meters

4	White	白
3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

Note:

- * @@Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF,Black
- * Pin: Copper Alloy,Gold Plated
- * Cable: UL2464 20AWG*4C+D+AL/My Black,PVC Jacket UV Resistant, OD=5.5
- △* Use with waterproof cap or dust cap
Panel Thickness Max: 2.0mm
- △* Use without waterproof cap or dust cap
Panel Thickness Max: 3.0mm
- △* Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE
TOLERANCE		Middle, Cable Lock 4 Pin M Conn. F Pin
±0.5 mm	SCALE Free	SHEET 1 OF 1
	REV. C	SIZE A4
		QC :Inspection Item

Amphenol LTW		ITEM NO	DRAWN BY	DATE
安費諾亮泰企業股份有限公司		DWG NO	Ruru	2016/03/14
		CUSTOMER	CHECKED BY	DATE
		ALTW	Rita	2016/03/14
			APPROVED BY	DATE
			Lisa	2016/03/14

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CB-04PMFM-LL7A05](#) [CB-04PMFM-LL7A02](#) [CB-04PMFM-LL7A01](#) [CB-04PMFM-LL7A10](#)