





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0198~201	2008/09/25	Shin	Add Note
C	LEN1630448~451	2016/03/11	Ruru	Change Logo & Note




Recommended
Panel Cut-Out



Pin Assignments
Front View

5	Green	綠
4	White	白
3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		



CB-05PMFM-SL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
:
99:99Meters

Cable Length(L):01~99Meters

Note:

- * QC Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 20AWG*5C+D+AL/My, PVC Jacket UV Resistant, OD=6.0, Black

* Use with waterproof cap or dust cap

Panel Thickness Max: 1.2mm

* Use without waterproof cap or dust cap

Panel Thickness Max: 2.0mm

* Cable Length Tolerance: 01M: ±40mm

02M~05M: ±60mm

06M~10M: ±100mm

11M~30M: ±200mm

31M~99M: ±500mm

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	Middle, Cable Screw 5 Pin M Conn. F Pin
SCALE	Free	SHEET 1 OF 1
REV. C	SIZE A4	QC : Inspection Item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CB-05PMFM-SL7A02](#) [CB-05PMFM-SL7A05](#) [CB-05PMFM-SL7A01](#) [CB-05PMFM-SL7A10](#)