


Conn.

Pin Assignments Front View



6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

CB-06AFFM-SL7AXX

```

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
.
.
.
99 : 99Meters

```

Cable Length(L):01~99Meters

△ Note:

- *  Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Screw Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 20AWG*6C+Drain+Al/My,
Black,PVC Jacket,UV Resistant,OD=6.5
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT: mm		
TOLERANCE		
$\pm 0.5 \text{ mm}$		

TITLE		Middle Cable Screw 6Pin F Conn F Pin	
SCALE	1:1	SIZE	A4
REV.	C	WC-REV.	A.1
		QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2014-07-28
DWG NO CB-06AFFM-SL7AXX	CHECKED BY Sam	DATE 2014-07-28
CUSTOMER ALTW	APPROVED BY Rita	DATE 2014-07-28

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1CB-06AFFM-SL7A01](#)