





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0044~47	2008/09/25	Shin	Add Note
C	LEN1630595~98	2016/03/18	Ruru	Change Logo & Note



Recommended
Panel Cut-Out



Pin Assignments
Front View

6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin Out	



CB-06PMMM-LL7AXX

XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters

Cable Length(L):01~99Meters

Note:

- * @@Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF,Black
- * Pin: Copper Alloy,Gold Plated
- * Cable: UL2464 20AWG*6C+D+AL/My Black,PVC Jacket UV Resistant, OD=6.5

- △* Use with waterproof cap or dust cap
Panel Thickness Max: 2.0mm
- △* Use without waterproof cap or dust cap
Panel Thickness Max: 3.0mm
- △* Cable Length Tolerance: 01M: ±40mm

02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE Middle, Cable Lock 6 Pin M Conn. M Pin
TOLERANCE ±0.5 mm	SCALE Free	SHEET 1 OF 1
REV. C	SIZE A4	QC :Inspection Item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2016/03/18
DWG NO CB-06PMMM-LL7AXX	CHECKED BY Rita	DATE 2016/03/18
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2016/03/18

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CB-06PMMM-LL7A02](#) [CB-06PMMM-LL7A10](#) [CB-06PMMM-LL7A05](#) [CB-06PMMM-LL7A01](#)