





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	FN-8B0104~107	2008/09/25	Shin	Add Note
C	FN1630289~292	2016/03/07	Ruru	Change Logo & Note



Recommended Panel Cut-Out



Pin Assignments Front View



6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

CB-06PMMM-SL7AXX
XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

- Note:
- * @@Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 20AWG*6C+D+AL/My, PVC Jacket UV Resistant, OD=6.5, Black
 - △* Use with waterproof cap or dust cap
Panel Thickness Max: 1.2mm
 - △* Use without waterproof cap or dust cap
Panel Thickness Max: 2.0mm
 - △* Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE
Middle, Cable Screw 6 Pin M Conn. M Pin		
TOLERANCE	SCALE	SHEET
±0.5 mm	Free	1 OF 1
REV. C	SIZE A4	QC :Inspection Item

ITEM NO		DRAWN BY	DATE
		Ruru	2016/03/07
DWG NO		CHECKED BY	DATE
CB-06PMMM-SL7AXX		Rita	2016/03/07
CUSTOMER		APPROVED BY	DATE
ALTW		Lisa	2016/03/07

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CB-06PMMM-SL7A10](#) [CB-06PMMM-SL7A05](#) [CB-06PMMM-SL7A01](#) [CB-06PMMM-SL7A02](#)