



Conn.

CBU-08AFDM-TL7AXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters

99 : 99Meters

Cable Length(L):01~99Meters



Conn.
Pin Assignments
Front View

8	Drain	24AWG	地線	Twist 對線
7	Green	24AWG	綠	
6	White/Green	24AWG	白 / 綠	Twist 對線
5	Orange	24AWG	橘	
4	White/Orange	24AWG	白 / 橘	Twist 對線
3	Blue	16AWG	藍	
2	Brown	16AWG	棕	
1	Green/Yellow	16AWG	綠 / 黃	
Conn.	Wire Color			
Pin Out				

Note:

- *  Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Lock Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 (24AWG*2P+D+AI/My)+16AWG*3C+F+P, Black,PVC Jacket,UV Resistant,OD=12.0
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE HyBrid Cable, Middle, 3Key 3FPin(10A)+5MPin(2A)			Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO	DRAWN BY Vicky	DATE 2014-08-20
TOLERANCE ±0.5 mm		SCALE 1:1	SIZE A4	SHEET 1 OF 1		DWG NO CBU-08AFDM-TL7AXX	CHECKED BY Sam	DATE 2014-08-20
		REV. B	MC-REV. A.1	QC: Inspection item		CUSTOMER ALTW	APPROVED BY Rita	DATE 2014-08-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CBU-08AFDM-TL7A10](#) [CBU-08AFDM-TL7A05](#) [CBU-08AFDM-TL7A01](#) [CBU-08AFDM-TL7A02](#) [CBU-08AFEM-](#)
[TL7A10](#) [CBU-08AFEM-TL7A02](#) [CBU-08AFEM-TL7A05](#) [CBU-08AFEM-TL7A01](#)