








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2011/07/26	Kevin Wang	
B	LEN1350051	2013/04/24	Ruru	Modify Cable OD Max



Note:

- * Important Dimension.
- * Waterproof Rate: IP67
- * Connector: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * O-Ring: EPDM, Black
- * Lock Nut: Nylon+GF, Black
- * Gasket: Silicone, Black
- * Clamp Ring: Nylon, Black
- * Seal: EPDM, Black
- * Sealing Nut: Nylon, Black
- * Cable OD Max : $\varnothing 7.6 \sim \varnothing 9.6 \text{mm}$

UNIT:mm



TOLERANCE
.X ± 0.25
.XX ± 0.1
.XXX ± 0.05
ANGLES $\pm 1^\circ$

TITLE

HyBrid Assy., Middle, 3Key
3FPin(10A)+5MPin(2A)

SCALE

1:1

SIZE

A4

SHEET

1 OF 1

REV.

B

WC-REV.

B.1

Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

CBU-08BFDA-TL7001

DWG NO

CBU-08BFDA-TL7001

CUSTOMER

ALTW

DRAWN BY

Ruru

CHECKED BY

Rita

APPROVED BY

Maslow

DATE

2013-05-06

DATE

2013-05-06

DATE

2013-05-06

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CBU-08BFDA-TL7001](#)