




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN15C0083	2015-12-01	Spring	Update the SR and note
C	LE31670031	2016-06-15	Tom_Gu	Change Part No. of Half Finished
D	LEN1710066	2017-01-10	Frank Deng	Change pin gender



Conn.

△ CC-02AFFM-QL8W0P
Color: Black

◎ White Printing
白色印刷




CC-02AFFM-QL8EXX



XX: 01~99Meters
01: 01Meter
02: 02Meters
...
99: 99Meters

Note:

- * ◎ Important Dimension To Check.
- * Working Voltage Rating: 300V AC
- * Working Current Rating: Max. 20A
- * Waterproof Rate: IP68.(Mated)
(in 1 meter water within 24 hours)
- * Connector: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Lock Nut: Nylon+GF, Black.
- * Cable: SJTW 12WG*2C, Black,
PVC Jacket, OD=10.7mm.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

2	White	白
1	Black	黑
Conn.	Wire Color	
	Pin Out	

UNIT:mm		TITLE	X Lok C-Size Cable 2 Pin 20A F Conn. F Pin △		
TOLERANCE	±0.5	SCALE	1:1	SIZE	A4
		REV.	D	WC-REV.	A.3
				◎	Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DWG NO	CUSTOMER	DRAWN BY	CHECKED BY	APPROVED BY	DATE
	CC-02AFFM-QL8EXX	ALTW	Frank Deng	Spring_Liu	Kevin_Hu	2017-01-10
						2017-01-10
						2017-01-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CC-02AFFM-QL8E05](#)