






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-9A0016~019	2009/04/14	Li Xiu Zhi	Change SR View & Update Note
C	LEN1480180~186	2014/08/05	Vicky	Update Logo



Conn.



Pin Assignments
Front View

3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

CC-03AFFM-LL7AXX

- XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters

Cable Length(L): 01~99Meters

Note:

- * Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Lock Nut: Nylon+GF, Black.
- * O-Ring: EPDM, Black.
- * Cable: UL2464 16AWG*3C+Drain+Al/My, Black, PVC Jacket, UV Resistant, OD=7.5
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	Middle Cable Lock 3Pin F Conn F Pin
SCALE	1:2	SIZE A4
REV.	C	WC-REV. A.1
		QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ALTW	Rita	2014-08-05

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1CC-03AFFM-LL7A01](#)