



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-9A0023~026	2009/04/14	Li Xiu Zhi	Change SR View & Update Note
C	LEN1480188~192	2014/08/05	Vicky	Update Logo




CC-03AFFM-SL7AXX

XX :01~99Meters
 01 :01Meter
 02 :02Meters
 ...
 99 :99Meters


Cable Length(L):01~99Meters

△Note:

- * CC Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Screw Nut: Nylon+GF, Black.
- * O-Ring: EPDM, Black.
- * Cable: UL2464 16AWG*3C+Drain+Al/My, Black,PVC Jacket,UV Resistant,OD=7.5
- * Cable Length Tolerance: 01M:±40mm
 02M~05M:±60mm
 06M~10M:±100mm
 11M~30M:±200mm
 31M~99M:±500mm



Conn.



Pin Assignments
Front View

3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	Middle Cable Screw 3Pin F Conn F Pin
SCALE	1:2	SIZE A4
REV.	C	WC-REV. A.1
SHEET 1 OF 1		
QC: Inspection item		

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ALTW	Vicky	2014-08-05
	Sam	2014-08-05
	Rita	2014-08-05

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1CC-03AFFM-SL7A01](#)