






7	White	白
6	Green	綠
5	Brown	棕
4	Red	紅
3	Yellow	黃
2	Orange	橘
1	Blue	藍
Conn.	Wire Color	
Pin Out		

CD-07AMMM-LL7AXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

Cable Length(L): 01~99Meters

 Note:

- *  Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24AWG*7C+Drain+Al/My, Black,PVC Jacket,UV Resistant,OD=5.8
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm			TITLE Middle Cable Lock 7Pin M Conn M Pin		Amphenol LTW		ITEM NO	DRAWN BY Vicky	DATE 2014-08-13
TOLERANCE ±0.5 mm			SCALE 1:1	SIZE A4	SHEET 1 OF 1	安費諾亮泰企業股份有限公司	DWG NO CD-07AMMM-LL7AXX	CHECKED BY Sam	DATE 2014-08-13
			REV. C	WC-REV. A.1	(QC): Inspection item		CUSTOMER ALTW	APPROVED BY Rita	DATE 2014-08-13
1		2		3		4		5	
6		7		8		9		10	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-07AMMM-LL7A10](#) [CD-07AMMM-LL7A01](#) [CD-07AMMM-LL7A02](#) [CD-07AMMM-LL7A05](#) [1CD-07AMMM-LL7A01](#)