


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C		05/29/2008	Ivan	Modify the holes & change pin
D	LEN-8B0170~173	2008/09/25	Shin	Add Note
E	LEN1630491~494	2016/03/15	Ruru	Change Logo & Note



Cable ② CD-07PMFM-LL7000
Color: Black


CD-07PMFM-LL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
:
99:99Meters


Cable Length(L):01~99Meters

Note:

- * @@Important Dimensions To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF,Black
- * Female Pin: Copper Alloy,Gold Plated
- * Cable: UL2464 24AWG*7C+D+AL/My, PVC Jacket UV Resistant, OD=5.8, Black
- * Use with waterproof cap or dust cap
Panel Thickness Max: 2.0mm
- * Use without waterproof cap or dust cap
Panel Thickness Max: 3.0mm
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm





Recommended
Panel Cut-Out



Pin Assignments
Front View

7	White	白	△
6	Green	綠	△
5	Brown	棕	△
4	Red	紅	△
3	Yellow	黃	△
2	Orange	橘	△
1	Blue	藍	△
Conn.	Wire Color		
	Pin Out		



UNIT:mm		TITLE
TOLERANCE	±0.5 mm	Middle, Cable Lock 7Pin M Conn F Pin
SCALE	Free	SHEET 1 OF 1
REV. E	SIZE A4	QC :Inspection Item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
	Ruru	2016/03/15
CD-07PMFM-LL7AXX	Rita	2016/03/15
ALTW	Lisa	2016/03/15

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-07PMFM-LL7A05](#) [CD-07PMFM-LL7A02](#) [CD-07PMFM-LL7A10](#) [CD-07PMFM-LL7A01](#)