







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0231	2008/10/03	Shin	Add Note
C	CI90271	2019/02/27	Ruru	Modify Note & Change Logo



Pin Assignments
Front View



Recommenderd Panel Cut-Out



- Note:
- * Important Dimension.
 - * Waterproof Rate: IP67, Unmated
 - * Housing: Thermoplastic, Black
 - * Pin: Copper Alloy, Gold Plated
 - * Nut: Thermoplastic, Black
 - * Gasket: Rubber, Black
 - * Use with waterproof cap or dust cap
Maximum Panel Thickness: 3.0mm
 - * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.0mm
 - * Gasket and Nut are packed separately in PE bags.

UNIT:mm		TITLE Middle, Panel Lock 7Pin M Conn. M Pin		
TOLERANCE		SCALE	SIZE	SHEET
.X ±0.25		1:1	A4	1 OF 1
.XX ±0.1		REV.	WC-REV.	
.XXX ±0.05		C	A.2	
ANGLES ±1°				Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	CD-07RMMS-LC7001	DRAWN BY	Ruru	DATE	2019-02-27
DWG NO	CD-07RMMS-LC7001	CHECKED BY	Rita	DATE	2019-02-27
CUSTOMER	ALTW	APPROVED BY	Max	DATE	2019-02-27

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1CD-07RMMS-LC7001](#)