


8	Green	綠
7	Yellow	黃
6	Orange	橘
5	Red	紅
4	Blue	藍
3	White	白
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

CD-08AFMM-LL7A_{XX}

```

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
      .
      .
      .
      .
99 : 99Meters

```

Cable Length(L):01~99Meters

Note:

- *  Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Lock Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 24AWG*8C+Drain+Al/My,
Black,PVC Jacket,UV Resistant,OD=5.5
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT: mm

TOLERANCE

± 0.5 mm

TITLE			
Middle Cable Lock 8Pin F Conn M Pin			
SCALE	1:1	SIZE	A4
REV.	C	WC-REV.	A.1
QC: Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2014-08-14
DWG NO CD-08AFMM-LL7AXX	CHECKED BY Sam	DATE 2014-08-14
CUSTOMER ALTW	APPROVED BY Rita	DATE 2014-08-14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1CD-08AFMM-LL7A01](#)