






Conn.



Recommended
Panel Cut-Out



Pin Assignments

8	Green	綠	△
7	Yellow	黃	△
6	Orange	橘	△
5	Red	紅	△
4	Blue	藍	△
3	White	白	△
2	Brown	棕	△
1	Black	黑	△
Conn.	Wire Color		
	Pin Out		

CD-08PMMM-SL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
 ⋮
 ⋮
 99:99Meters

Cable Length(L):01~99Meters

Note:

- * @C Important Dimensions To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF,Black
- * Male Pin: Copper Alloy,Gold Plated
- * Cable: UL2464 24AWG*8C+D+AL/My
Black,PVC Jacket UV Resistant, OD=5.5
- * Use with waterproof cap or dust cap
Panel Thickness Max: 1.2mm
- * Use without waterproof cap or dust cap
Panel Thickness Max: 2.0mm
- * Cable Length Tolerance: 01M: $\pm 40\text{mm}$
02M~05M: $\pm 60\text{mm}$
06M~10M: $\pm 100\text{mm}$
11M~30M: $\pm 200\text{mm}$
31M~99M: $\pm 500\text{mm}$

UNIT:mm	
TOLERANCE	
$\pm 0.5 \text{ mm}$	

TITLE			
Middle, Cable Screw 8Pin M Conn M Pin			
SCALE		Free	SHEET 1 OF 1
REV.	D	SIZE A4	@@ : Inspection Item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2016/04/28
DWG NO CD-08PMMM-SL7AXX	CHECKED BY Rita	DATE 2016/04/28
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2016/04/28

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-08PMMM-SL7A02](#) [CD-08PMMM-SL7A05](#) [CD-08PMMM-SL7A10](#) [CD-08PMMM-SL7A01](#)