



		2		3		4		5		6		7		8	
				REV.		ECN NO.		DATE		SIGN		DESCRIPTION			
				B		LEN-9A0122~126		2009/04/17		Li Xiu Zhi		Change SR View & Update Note			
				C		LEN1480574~579		2014/08/22		Vicky		Update Logo			




Conn.









Pin Assignments
Front View

10	Orange	橘
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

CD-10AFFM-LL7AXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters

Cable Length(L): 01~99Meters

Note:

- * Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Lock Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 24AWG*10C+Drain+Al/My, Black,PVC Jacket,UV Resistant,OD=6.5
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm

TOLERANCE

±0.5 mm



TITLE

Middle Cable Lock 10Pin F Conn F Pin

SCALE	1:1	SIZE	A4	SHEET	1	OF	1
REV.	C	WC-REV.	A.1	: Inspection item			

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DWG NO	CUSTOMER
	CD-10AFFM-LL7AXX	ALTW

DRAWN BY	CHECKED BY	APPROVED BY
Vicky	Sam	Rita

DATE	DATE	DATE
2014-08-22	2014-08-22	2014-08-22

FWW10702-01-02A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1CD-10AFFM-LL7A01](#) [1CD-10AFFM-LL7A03](#)