




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0073~76	2008/09/25	Shin	Add Note
C	LEN1630531~534	2016/03/17	Ruru	Change Logo & Note




Cable ② CD-10PMMM-LL7000 ①
Color: Black

Conn.



Recommended
Panel Cut-Out



Pin Assignments
Front View



CD-10PMMM-LL7AXX
XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

5	Yellow	黃	10	Orange	橘
4	Green	綠	9	Black	黑
3	White	白	8	Red	紅
2	Blue	藍	7	Pink	粉紅
1	Brown	棕	6	Gray	灰
Conn. Wire Color		Conn. Wire Color		Pin Out	

- Note:
- * $\textcircled{C}$ Important Dimensions To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF,Black
 - * Male Pin: Copper Alloy,Gold Plated
 - * Cable: UL2464 24AWG*10C+D+AL/My Black,PVC Jacket UV Resistant, OD=6.5
 - * $\triangle$ Use with waterproof cap or dust cap
Panel Thickness Max: 2.0mm
 - * $\triangle$ Use without waterproof cap or dust cap
Panel Thickness Max: 3.0mm
 - * $\triangle$ Cable Length Tolerance: 01M: $\pm 40\text{mm}$
02M~05M: $\pm 60\text{mm}$
06M~10M: $\pm 100\text{mm}$
11M~30M: $\pm 200\text{mm}$
31M~99M: $\pm 500\text{mm}$

UNIT:mm		TOLERANCE		Middle, Cable Lock 10Pin M Conn M Pin		SCALE Free		SHEET 1 OF 1		REV. C		SIZE A4		$\textcircled{C}$:Inspection Item		Amphenol LTW		安費諾亮泰企業股份有限公司		ITEM NO		DWG NO		CUSTOMER		DRAWN BY		CHECKED BY		APPROVED BY		DATE		DATE		DATE	
$\pm 0.5 \text{ mm}$																						CD-10PMMM-LL7AXX		ALTW		Ruru		Rita		Lisa		2016/03/17		2016/03/17		2016/03/17	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-10PMMM-LL7A05](#) [CD-10PMMM-LL7A02](#) [CD-10PMMM-LL7A01](#) [CD-10PMMM-LL7A10](#)