





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B		2007/03/21	Ivan	Change Ø20.45+0/-0.25 to Ø20.60+0/-0.25
C	LEN-8B0136~139	2008/09/25	Shin	Add Note
D	LEN1630259~262	2016/03/01	Ruru	Change Logo & Note




CD-10PMMM-SL7000 ① 13/16"-28UN
Color: Black



Recommended Panel Cut-Out



Pin Assignments
Front View



CD-10PMMM-SL7AXX
XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

5	Yellow	黃	10	Orange	橘
4	Green	綠	9	Black	黑
3	White	白	8	Red	紅
2	Blue	藍	7	Pink	粉紅
1	Brown	棕	6	Gray	灰
Conn.	Wire Color		Conn.	Wire Color	

Pin Out

Note:

- * @C Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24AWG*10C+Drain+Al/My, PVC Jacket UV Resistant, OD=6.5mm, Black
- * Use with waterproof cap or dust cap
Panel Thickness Max: 1.2mm
- * Use without waterproof cap or dust cap
Panel Thickness Max: 2.0mm
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE	Middle	Amphenol LTW	ITEM NO	DRAWN BY	DATE
TOLERANCE		Cable Screw 10Pin M Conn M Pin		安費諾亮泰企業股份有限公司	DWG NO	Ruru	2016/03/01
±0.5 mm		SCALE Free	SHEET 1 OF 1		CD-10PMMM-SL7AXX	CHECKED BY	DATE
		REV. D	SIZE A4	@C :Inspection Item	CUSTOMER	Rita	2016/03/01
					ALTW	APPROVED BY	DATE
						Lisa	2016/03/01

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-10PMMM-SL7A02](#) [CD-10PMMM-SL7A05](#) [CD-10PMMM-SL7A10](#) [CD-10PMMM-SL7A01](#)