





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-9A0144~147	2009/04/17	Li Xiu Zhi	Change SR View & Update Note
C	LEN1490009~012	2014/08/25	Vicky	Update Logo



Conn.



Pin Assignments
Front View

12	Light Green	淺綠
11	Purple	紫
10	Orange	橘
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

CD-12AFFM-SL7A~~XX~~

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters

Cable Length(L): 01~99Meters

Note:

- * CC Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Screw Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 24AWG*12C+Drain+Al/My, Black, PVC Jacket, UV Resistant, OD=7.0
- * Cable Length Tolerance:
 - 01M: ±40mm
 - 02M~05M: ±60mm
 - 06M~10M: ±100mm
 - 11M~30M: ±200mm
 - 31M~99M: ±500mm

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	Middle Cable Screw 12Pin F Conn F Pin
SCALE	1:1	SIZE A4
REV.	C	WC-REV. A.1
SHEET 1 OF 1		
CC: Inspection item		

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Vicky	2014-08-25
CUSTOMER	CHECKED BY	DATE
ALTW	Sam	2014-08-25
	APPROVED BY	DATE
	Rita	2014-08-25

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1CD-12AFFM-SL7A01](#)