




| REV. | ECN NO.       | DATE       | SIGN | DESCRIPTION        |
|------|---------------|------------|------|--------------------|
| B    | LEN-8B0085~88 | 2008/09/25 | Shin | Add Note           |
| C    | LEN1630541~44 | 2016/03/17 | Ruru | Change Logo & Note |
|      |               |            |      |                    |




Cable ② CD-14PMMM-LL7000 ①  
Color: Black

CD-14PMMM-LL7AXX  
XX:01~99Meter  
01:01Meter  
02:02Meters  
...  
99:99Meters  
Cable Length(L):01~99Meters



Recommended  
Panel Cut-Out



Pin Assignments  
Front View

|       |            |    |       |              |     |
|-------|------------|----|-------|--------------|-----|
| 7     | Pink       | 粉紅 | 14    | Brown/White  | 棕/白 |
| 6     | Gray       | 灰  | 13    | Black /White | 黑/白 |
| 5     | Yellow     | 黃  | 12    | Light Green  | 淺綠  |
| 4     | Green      | 綠  | 11    | Purple       | 紫   |
| 3     | White      | 白  | 10    | Orange       | 橘   |
| 2     | Blue       | 藍  | 9     | Black        | 黑   |
| 1     | Brown      | 棕  | 8     | Red          | 紅   |
| Conn. | Wire Color |    | Conn. | Wire Color   |     |

- Note:
- \* @@ Important Dimensions To Check.
  - \* Waterproof Rate: IP67
  - \* Housing: Nylon+GF,Black
  - \* Male Pin: Copper Alloy,Gold Plated
  - \* Cable: UL2464 24AWG\*14C+D+AL/My Black,PVC Jacket UV Resistant, OD=7.0
  - △\* Use with waterproof cap or dust cap  
Panel Thickness Max: 2.0mm
  - △\* Use without waterproof cap or dust cap  
Panel Thickness Max: 3.0mm
  - △\* Cable Length Tolerance: 01M: ±40mm  
02M~05M: ±60mm  
06M~10M: ±100mm  
11M~30M: ±200mm  
31M~99M: ±500mm

|                                 |                                                |                 |                                      |                            |                    |                     |
|---------------------------------|------------------------------------------------|-----------------|--------------------------------------|----------------------------|--------------------|---------------------|
| UNIT:mm<br>TOLERANCE<br>±0.5 mm | TITLE<br>Middle, Cable Lock 14Pin M Conn M Pin |                 | <b>Amphenol LTW</b><br>安費諾亮泰企業股份有限公司 | ITEM NO                    | DRAWN BY<br>Ruru   | DATE<br>2016/03/17  |
|                                 | SCALE<br>Free                                  | SHEET<br>1 OF 1 |                                      | DWG NO<br>CD-14PMMM-LL7AXX | CHECKED BY<br>Rita | DATE<br>2016/03/17  |
|                                 | REV.<br>C                                      | SIZE<br>A4      |                                      | QC : Inspection Item       | CUSTOMER<br>ALTW   | APPROVED BY<br>Lisa |

12345678

FWI0702-01-01A2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-14PMMM-LL7A10](#) [CD-14PMMM-LL7A05](#) [CD-14PMMM-LL7A01](#) [CD-14PMMM-LL7A02](#)