



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	FN-8B0148~151	2008/09/25	Shin	Add Note
C	FN1630270~273	2016/03/07	Ruru	Change Logo & Note




Cable ②

CD-14PMMM-SL7000 ①
Color: Black


CD-14PMMM-SL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

- Note:
- * @@ Important Dimensions To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF,Black
 - * Male Pin: Copper Alloy,Gold Plated
 - * Cable: UL2464 24AWG*14C+D+AL/My Black,PVC Jacket UV Resistant, OD=7.0
 - △* Use with waterproof cap or dust cap
Panel Thickness Max: 1.2mm
 - △* Use without waterproof cap or dust cap
Panel Thickness Max: 2.0mm
 - △* Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm



Recommended
Panel Cut-Out



Pin Assignments
Front View

7	Pink	粉紅	14	Brown/White	棕/白
6	Gray	灰	13	Black /White	黑/白
5	Yellow	黃	12	Light Green	淺綠
4	Green	綠	11	Purple	紫
3	White	白	10	Orange	橘
2	Blue	藍	9	Black	黑
1	Brown	棕	8	Red	紅
Conn. Wire Color		Conn. Wire Color		Pin Out	



UNIT:mm				TITLE Middle, Cable Screw 14Pin M Conn M Pin Amphenol LTW 安費諾亮泰企業股份有限公司			ITEM NO		DRAWN BY Ruru		DATE 2016/03/07							
TOLERANCE ±0.5 mm							SCALE Free		SHEET 1 OF 1		DWG NO CD-14PMMM-SL7AXX		CHECKED BY Rita		DATE 2016/03/07			
							REV. C		SIZE A4		QC :Inspection Item		CUSTOMER ALTW		APPROVED BY Lisa		DATE 2016/03/07	
							1		2		3		4		5		6	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-14PMMM-SL7A05](#) [CD-14PMMM-SL7A01](#) [CD-14PMMM-SL7A02](#) [CD-14PMMM-SL7A10](#)