







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1580178~79	2015/08/08	Lu Di	Change To Common Drawing
C	LEN15B0376~380	2015/11/10	Joyy	Add 7-8 And 9 Pin To The Common Drawing



CD-XXAMMM-RR7000
Color: Black

2 Cable



- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: M-PPE, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Gasket: Silicone, Gray.
 - * Cable: UL2464 20#, PVC Jacket, UV Resistant, Black.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm
 - * Prohibiting the use of place in oils

B/C

CD-02AMMM-RR7AXX	Ø 5.5
CD-03AMMM-RR7AXX	
CD-04AMMM-RR7AXX	
CD-05AMMM-RR7AXX	Ø 6.0
CD-06AMMM-RR7AXX	Ø 6.5
CD-07AMMM-RR7AXX	
CD-08AMMM-RR7AXX	Ø 6.8
CD-09AMMM-RR7AXX	Ø 7.4
Part No.	Cable OD

UNIT:mm	
TOLERANCE	±0.5

TITLE MIDDLE CABLE RBL M CONN M PIN			
SCALE 1:1	SIZE A4	SHEET 1 OF 2	
REV. C	WC-REV. A.2	$\varnothing$: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Joyy	DATE 2015-11-10
DWG NO CD-XXAMMM-RR7AXX	CHECKED BY Lu Di	DATE 2015-11-10
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-11-10

B

F

E

D



C

C

B

A

B



CD-XXAMMM-RR7A XX

Middle Size Current Rating 5A

XX:No. Of Pin(Pin 數)

A:Cable With S/R(線端帶網尾)

M:Male Connector(公座)

M:Male Pin(公Pin)

M:Molding Type(射出成型)

XX:01~99Meter

01:01Meter

02:02Meter

...

99:99Meter

A:UL 2464 Cable

7:IP67(防水等級 67)

R:Right Angle(90°)

R:Snap In With Latch(彈臂卡合)

9 White 白

8 Purple 紫

7 Red 紅

6 Green 綠

5 Yellow 黃

4 Blue 藍

3 Orange 橘

2 Brown 棕

1 Black 黑

9 --

8 Purple 紫

7 Red 紅

6 Green 綠


5 Yellow 黃

4 Blue 藍


3 Orange 橘

2 Brown 棕

1 Black 黑



9Pin



8Pin

Pin Out

4 --

3 White 白

2 --

1 Black 黑

4 Blue 藍

3 White 白

2 --

1 Black 黑

4 Blue 藍

3 White 白

2 Brown 棕

1 Black 黑

6 Green 綠

5 --

4 Black 黑

3 Blue 藍

2 White 白

1 Brown 棕

6 Grey 灰

5 Yellow 黃

4 Green 綠

3 White 白

2 Blue 藍

1 Brown 棕

9 --

8 --

7 Red 紅

6 Green 綠


5 Yellow 黃

4 Blue 藍


3 Orange 橘

2 Brown 棕


1 Black 黑

Pin
Assignments
Front View


2Pin




3Pin




4Pin



5Pin




6Pin



7Pin

UNIT:mm

TOLERANCE
±0.5

TITLE

MIDDLE
CABLE RBL M CONN M PINSCALE
1:1SIZE
A4SHEET
2 OF 2REV.
CWC-REV.
A.2

QC:Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG. NO

CD-XXAMMM-RR7AXX

CUSTOMER

ALTW

DRAWN BY

Joyy

CHECKED BY

Lu Di

APPROVED BY

Jerry

DATE

2015-11-10

DATE

2015-11-10

DATE

2015-11-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-06AMMM-RR7A01](#) [CD-04AMMM-RR7A01](#) [CD-03AMMM-RR7A01](#) [CD-02AMMM-RR7A01](#) [CD-08AMMM-RR7A01](#) [CD-07AMMM-RR7A01](#) [CD-09AMMM-RR7A01](#) [CD-05AMMM-RR7A01](#)