










- Note:
- * Waterproof Rate: IP68
 - * Screw Nut: Nylon, Gray
 - * Clamp Ring: Nylon, Gray
 - * Sealing Nut: Nylon, Gray
 - * Gasket: EPDM, Black
 - * Seals: EPDM, Black
 - * Cable Range: $\varnothing 18 \sim \varnothing 25 \text{mm}$
 - * For Panel Thickness: 6.0mm max
 - * Spanner Size:
 - Body: 41.0mm
 - Sealing Nut: 42.2mm
 - Screw Nut: 46.0mm

UNIT:mm		TITLE		Amphenol LTW		ITEM NO		DRAWN BY		DATE	
TOLERANCE		Cable Gland Assembly(PG29)		安費諾亮泰企業股份有限公司		CSG-29G004		Ruru		2015-05-26	
.X		SCALE	4:5	SIZE	A4	DWG NO		CHECKED BY		DATE	
.XX		REV.	C	WC-REV.	A.1	CSG-29G004		Rita		2015-05-26	
.XXX		QC:Inspection item		CUSTOMER		ALTW		APPROVED BY		DATE	
ANGLES								Lion		2015-05-26	
										FMW10702-01-02A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CSG-29G004](#)