








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1570060	2015/06/02	Ruru	Change Logo



Section A-A



Note:

- * Waterproof Rate: IP68
- * Screw Nut: Nylon, Black
- * Clamp Ring: Nylon, Black
- * Sealing Nut: Nylon, Black
- * Gasket: EPDM, Black
- * Seals: EPDM, Black
- * For Panel Thickness: 9.0mm max
- * Cable Range: $\varnothing 20 \sim \varnothing 25$ mm
- * Spanner Size:
 - Body: 50.3mm
 - Sealing Nut: 51.7mm
 - Screw Nut: 50.0mm

UNIT:mm		 	TITLE Cable Gland Assembly(M40*1.5)			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO CSG-40M001		DRAWN BY Ruru		DATE 2015-06-02		
TOLERANCE ±0.5 mm			SCALE 1:2		SIZE A4			DWG NO CSG-40M001		CHECKED BY Rita		DATE 2015-06-02		
			SHEET 1		OF 1			CUSTOMER ALTW		APPROVED BY Lion		DATE 2015-06-02		
			REV. B		WC-REV. A.1		QC: Inspection item							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CSG-40M001](#)