









- * Waterproof Rate: IP68
- * Screw Nut: Nylon, Gray
- * Clamp Ring: Nylon, Gray
- * Sealing Nut: Nylon, Gray
- * Gasket: EPDM, Black
- * Seals: EPDM, Black
- * For Panel Thickness: 9.0mm max
- * Cable Range: $\varnothing 20\sim\varnothing 25\text{mm}$
- * Spanner Size:
 - Body: 50.3mm
 - Sealing Nut: 51.7mm
 - Screw Nut: 50.0mm



UNIT:mm			TITLE Cable Gland Assembly(M40*1.5)			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO CSG-40M002		DRAWN BY Ruru		DATE 2015-06-02							
TOLERANCE ±0.5 mm								SCALE 1:2		SIZE A4		SHEET 1 OF 1		DWG NO CSG-40M002		CHECKED BY Rita		DATE 2015-06-02	
								REV. B		WC-REV. A.1		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Lion		DATE 2015-06-02	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CSG-40M002](#)