

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1390051	2013-08-28	Micky	Add Certification Information





△ CC Laser Mark:  
YYYY = Year  
WW = Week


④ Unlock Tool  
△ Part number: ULT-JOIN01

△ Cable Joiner Housing Part Number  
CX-00B0M32-700X

M32x1.0




\* Recommended sealing Nut torque  
Minimum: 25Kgf-cm



Note:  
\* Waterproof Rate: IP67  
\* Connector: PPE,Black(UL94-V0 FI )  
\* Butt Pin: Copper alloy  
\* Gasket: Silicon,Gray  
\* Disassembly-Using the Unlock tool.  
\* Operating Temperature : -40~+105°C  
\* Withstanding Voltage : 6KV  
\* Pollution Degree : III  
\* Cable OD Range: 10mm~08mm  
\* Avoid oil and gasoline

△ \* CX-00B0M32-700X  
UL 6703A & TUV 2pfg 1915



UNIT:mm		TITLE Cable joiner Cable OD Range: 10mm~08mm(4 Conductor)		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO CX-00B0M32-7003	DRAWN BY Micky	DATE 2013-08-28
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 4:5	SIZE A4	SHEET 1 OF 1		DWG NO CX-00B0M32-7003	CHECKED BY Benson	DATE 2013-08-28
REV. B		WC-REV. B.1	QC: Inspection item			CUSTOMER ALTW	APPROVED BY Victor	DATE 2013-08-28

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CX-00B0M32-7003](#)