

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1390052	2013-08-28	Micky	Add Certification Information





△QC Laser Mark:
YYYY = Year
WW = Week

5 Unlock Tool
△B Part number: ULT-JOIN01


△B Cable Joiner Housing Part Number
CX-00B0M32-700X

M32x1.0



130.3(Ref.)

* Recommended sealing Nut torque
Minimum: 25Kgf-cm



△B * CX-00B0M32-700X
UL 6703A & TUV 2pfg 1915
* Butt Terminals
UL 486A/B

Note:

- * Waterproof Rate: IP67
- * Connector: PPE,Black(UL94-V0 FI)
- * Butt Pin: Copper alloy
- * Gasket: Silicon,Gray
- * Disassembly-Using the Unlock tool.
- * Operating Temperature : -40~+105°C
- * Withstanding Voltage : 6KV
- * Pollution Degree : III
- * Cable OD Range: 10mm~08mm
- * Wire Range: 14#~16#(2.5mm²~1mm²)
- * Avoid oil and gasoline

UNIT:mm



TOLERANCE
.X ±0.5

TITLE			
Cable joiner 14#~16#(2.5mm ² ~1mm ²)			
Cable OD Range: 10mm~08mm(4 Conductor)			
SCALE	SIZE	SHEET	OF
4:5	A4	1	1
REV.	WC-REV.	QC: Inspection item	
B	B.1		

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
CX-04BBM32-7001	Micky	2013-08-28
DWG NO	CHECKED BY	DATE
CX-04BBM32-7001	Benson	2013-08-28
CUSTOMER	APPROVED BY	DATE
ALTW	Victor	2013-08-28

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CX-04BBM32-7001](#)