

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1390056	2013-08-28	Micky	Add Certification Informatuon





QC Laser Mark:
YYYY = Year
WW = Week

Unlock Tool
Part number: ULT-JOIN01


Cable Joiner Housing Part Number
CX-00B0M32-700X

M32x1.0




130.5(Ref.)

* Recommended sealing Nut torque
Minimum: 25Kgf-cm



Note:
* Waterproof Rate: IP67
* Connector: PPE,Black(UL94-V0 FI)
* Butt Pin: Copper alloy
* Gasket: Silicon,Gray
* Disassembly-Using the Unlock tool.
* Operating Temperature : -40~+105°C
* Withstanding Voltage : 6KV
* Pollution Degree : III
* Cable OD Range: 12mm~10mm
* Wire Range: 10#~12#(4mm²~6mm²)
* Avoid oil and gasoline

* CX-00B0M32-700X
UL 6703A & TUV 2pfg 1915
* Butt Terminals
UL 486A/B



UNIT:mm		TITLE Cable joiner 10#~12#(4mm ² ~6mm ²) Cable OD Range: 12mm~10mm(4 Conductor)	
TOLERANCE .X	±0.5	SCALE 4:5	SIZE A4
REV. B	WC-REV. B.1	SHEET 1	OF 1
QC:Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO CX-04BCM32-7002	DRAWN BY Micky	DATE 2013-08-28
DWG NO CX-04BCM32-7002	CHECKED BY Benson	DATE 2013-08-28
CUSTOMER ALTW	APPROVED BY Victor	DATE 2013-08-28

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CX-04BCM32-7002](#)