




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2017-03-15	Frank Deng	Change Rev.01 To Rev.A
B	LEN1770174	2017-07-03	Frank Deng	Change Note



Conn.



HPC-05BMMM-SL8AXX
T
XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters
Cable Length(L): 01~99Meters



Conn.
Pin Assignments
Front View

5	Blue 藍	24#	Twist
4	White 白	24#	
3	Black 黑	22#	Twist
2	Red 紅	22#	
1	Drain 地線	22#	
Conn.	Wire Color		
Pin Out			

- △ Note:
- * Ⓞ Important Dimension To Check.
 - * Waterproof Rate: IP68
In 1 meter water within 24 hours
 - * Connector: PU, Black
 - * Nut: Nylon, Black
 - * M Pin: Copper Alloy, Gold Plated 30u"
 - * Outer Mold: PU, Blue
 - * Cable: CL2, (24#*1P+A/M)+(22#*1P+A/M)+
D+B, PVC UV Cable, OD=6.7mm, Black
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
±0.5mm				NMEA 2000 SINGLE ENDED CABLE MICRO-C, M CONN M PIN, PLASTIC		HPC-05BMMM-SL8AXX		Frank Deng		2017-07-06	
				SCALE 3:2		SIZE A4		CHECKED BY Fisher Wang		DATE 2017-07-06	
				REV. B		WC-REV. A.2		APPROVED BY Kevin Hu		DATE 2017-07-06	
				SHEET 1 OF 1		CUSTOMER ALTW					
				QC: Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HPC-05BMMM-SL8A02](#)