



REV	ECN	APP'D
-	6582	<i>JA 9/10/10</i>



WHITE MARKING  
.06 HT

DATE CODE



#### NOTES:

##### 1. MATERIALS:

HOUSING: POLYETHERIMIDE, COLOR BLACK

GROMMET: SILICONE ELASTOMER, COLOR BLUE

INTERNAL CONTACT: COPPER ALLOY, GOLD PLATED,  
PER MIL-DTL-45204, TYPE I, GRADE C, CLASS I




50 MICROINCH MIN. OVER NICKEL PER SAE-AMS-QQ-N-290,  
CLASS 1, 50/30 MICROINCH MIN.

CONTACT RETAINER: STAINLESS STEEL

2. SPLICE ACCEPTS (4) MATING M39029/I-100 CONTACTS  
(INCLUDED)

3. PART COMPLIES TO ALL REQUIREMENTS PER SAE-AS81714.

4. RESISTOR:  $4.99\Omega$ , 1/4W,  $\pm 1\%$ , RLR07C4R99FM

<div>DIMENSIONS</div> <div>ANSI Y14.5M</div> <div>UNITS: INCHES</div> <div>Pro/E FILE</div>	<div>TOLERANCES</div> <div>.XX ±0.01</div> <div>.XXX ±0.005</div> <div>ANGLES ±2.0°</div>	<div>PROJECTION</div> <div></div>	<div>Amphenol Pcd</div> <div>SPECIFICATION DRAWING</div> <div>ENGR</div> <div>M. DiGIACOMO 08/12/09</div>	<div>TITLE</div> <div>WIRE SPLICE, ELECTRONIC</div> <div>RESISTOR, 4.99Ω, 1/4W, 1%</div> <div>SIZE 22</div>			
<div>ORIGINAL</div>	<div>THIS DOCUMENT CONTAINS</div> <div>PROPRIETARY INFORMATION WHICH</div> <div>IS THE CONFIDENTIAL PROPERTY</div> <div>OF AMPHENOL PCD</div> <div>BEVERLY, MA, USA</div>		<div>CHKD</div> <div></div> <div>APPD</div> <div></div>	<div>SIZE</div> <div>A</div>	<div>DWG NO.</div> <div>TJSE22839_C</div>	<div>REV</div> <div>-</div>	
			<div>CODE:</div> <div>58982</div>	<div>SCALE:</div> <div>2:1</div>	<div>SHEET 1 OF 1</div>		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TJSE22839](#)