

WSB™ Weather Seal Strain Relief Boots

For LMR®-195-200, LMR®-240,
LMR®-400 & LMR®-600

ISO 9001 Certified

- *Combination strain relief and weather seal boot*
- *Eliminates the need for a heat gun to shrink the standard heat shrink sleeve*
- *Fits the most popular LMR®-195-200, 240, 400 & 600 EZ connectors*
- *IP-67 rated*
- *Convenient 10 pack*



The WSB™ weather seal strain relief boots work with the most popular EZ crimp connectors for LMR®-195-200, 240, 400 and 600.

The soft silicone boot weatherproofing kits replace older weatherproofing methods, require no heat and only simple and easy hand assembly for valuable time saving in the field.

The WSB™ weather seal strain relief boots are IP67 rated and both RoHS and REACH Compliant.

Supplied in a convenient 10 pack, the WSB™ kits contain four pouches of silicone lubricant to facilitate installation of the boots.

WSB™ Weather Seal Strain Relief Boots

Connector Compatability							
WSB-195-200		WSB-240		WSB-400		WSB-600	
Part #	Description	Part #	Description	Part #	Description	Part #	Description
3190-6140 - EZ-195-SM-X		3190-2726 - EZ-240-TM-RA-X		3190-2524 - EZ-400-716M-X		3190-2642 - TC-600-716M-X	
3190-6141 - EZ-195-BM-X		3190-2868 - EZ-240-BM-RA-X		3190-2597 - TC-400-716M-X		3190-2546 - EZ-600-716M-RA-X	
3190-2880 - TC-195-NMH-X		3190-2893 - EZ-240-NMH-X		3190-2545 - EZ-400-716M-RA-X		3190-2816 - TC-600-NF-X	
3190-2425 - TC-195-NMH-RA-D		3190-2894 - EZ-240-QM-X		3190-2590 - EZ-400-NMH-X		3190-2817 - EZ-600-NF-X	
3190-2878 - TC-195-SM-SS-X		3190-2897 - EZ-240-SM-X		3190-2626 - TC-400-NMH-X		3190-2627 - EZ-600-NMH-X	
3190-2879 - TC-195-TM-X		3190-6143 - EZ-240-NMH-RA-X		3190-2293 - TC-400-NMH-RA-D		3190-2628 - TC-600-NMH-X	
3190-6384 - EZ-195-QF-X		3190-6204 - EZ-240-TF-X		3190-3049 - EZ-400-TF-X		3190-6123 - EZ-600-QNM-X	
3190-6208 - EZ-195-QNM-X		3190-2896 - TC-240-SF-BH-SS-X		3190-3051 - TC-400-TF-X		3190-6136 - TC-600-SCM-X	
3190-6166 - EZ-195-TF-RP-X		3190-2898 - TC-240-SM-SS-X		3190-2533 - EZ-400-TM-X		3190-3050 - EZ-600-TF-X	
3190-6142 - EZ-195-TM-RP-X				3190-2532 - TC-400-TM-X		3190-3052 - TC-600-TF-X	
3190-6007 - EZ-200-SF-SS-X				3190-2800 - EZ-400-TM-RA-X		3190-2531 - EZ-600-TM-X	
3190-2882 - TC-200-NMH-X				3190-2818 - EZ-400-NF-X		3190-2530 - TC-600-TM-X	
3190-2886 - EZ-200-NMH-X				3190-2815 - TC-400-NF-X			
3190-2883 - TC-200-BM-X				3190-2803 - EZ-400-NF-PM-X			
3190-6006 - EZ-200-SM-RA-SS-X				3190-2805 - TC-400-NF-PM-X			
3190-2884 - TC-200-TF-X				3190-2852 - EZ-400-BM-X			
3190-2885 - EZ-200-TM-X				3190-2847 - EZ-400-BM-RA-X			
3190-6008 - EZ-200-TM-RA-X				3190-2961 - EZ-400-NMH-PL-X			
				3190-2962 - TC-400-NMH-PL-X			
				3190-2969 - EZ-400-4195M-X			
				3190-2968 - EZ-400-4195F-X			
				3190-2979 - EZ-400-QNM-X			
				3190-2980 - EZ-400-QNF-X			
				3190-2981 - EZ-400-QNM-RA-X			
				3190-6011 - EZ-400-QNF-BH-X			

Mechanical/Environmental Specifications		
	Test Method	Value
Hardness	DIN 53505	Shore A
Density at 20°C	DIN 51757	1.19 g/cm ³
Elongation at Break	DIN 53504 S1	300%
Rebound Resilience	DIN 53512	50%
Tear Strength	ASTM D624-B	18 N/mm
Compression Set	DIN ISO 815-B	12%
Operating Temperature		-40°C to 85°C

Construction:

Material: Silicone rubber

Color: Black

Lubricant: Silicone grease

Ordering information:

Part Number - Stock Code

WSB-195-200 3109-445

WSB-240 3109-400

WSB-400 3109-394

WSB-600 3109-401



World Headquarters: 358 Hall Avenue, Wallingford, CT 06492 • Tel: 203-949-8400, 1-800-867-2629 Fax: 203-949-8423

International Sales: +1 203-949-8503 • +1 800-867-2629

China Sales: TMC Building 4, No. 318 Yuanshan Road, Xinzhuang Industrial Park, Shanghai, China 201108 Tel: 86-21-5176-1209 Fax: 86-21-64424098
www.timesmicrowave.com

© 2017, Times Microwave Systems, Wallingford, CT 06492

WSB-06/17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[WSB-195-200](#) [WSB-240](#) [WSB-400](#) [WSB-600](#)