





SIGN	DATE	DESCRIPTION	APPROVER
△	01/20'07	The Soldering temperature from 245° to 250°	Aaron
△	2010.08.12	The design is changed	Chen Bo
△	2012.07.18	The tolerance are added	Runner

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!



P.C.B. LAYOUT

△ N = Number of poles
 Dim L = (N x 5.08) + 2.54
 Dim P = (N - 1) x 5.08

Poles	Dim L	Dim P
2-6p	±0.20	
7-12p	±0.25	
13-24p	±0.40	

Material

- Terminal lever: Thermoplastic (UL94 V-0) Orange RAL2011/P
- Terminal housing: Thermoplastic (UL94 V-0)
- Terminal cover: Thermoplastic (UL94 V-0)
- Solder Pin : Brass Tin plated
- Wire guard: Stainless steel

Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 10A/10A
- Wire range: 0.75-1.5mm²
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ± 10°C / 5 Sec
- Safety Approval:

- Critical dimension:

HA xx 00 x 0 xxxx G

- 02 2 Poles
- 03 3 Poles
-
- 24 24 Poles

Body color

- 2 Red
- 3 Orange
- 5 Green(RAL6018/T)
- 8 Grey(RAL7004/P)

RoHS compliant (lead<4%)
 In copper Alloy
 0000: "@ Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HA-5.08mm 90° series			
PART NO.		HAxx00x0xxxxG		DWG NO.	8HA0101
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.
		Runner 2012.07.18	Chen Bo 2010.08.12		
					Tolerance
					X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°
SHEET: 01/01					UNIT: mm
					SCALE: NONE
					REV.: F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[20020302-H021B01LF](#) [20020302-H031B01LF](#) [20020302-H041B01LF](#) [HA03005000J0G](#) [HA04005000J0G](#)
[HA02005000J0G](#) [HA2100500000G](#) [HA0600500000G](#) [HA1600500000G](#) [HA2400500000G](#) [HA1200500000G](#)
[HA0900500000G](#) [HA1400500000G](#) [HA1300500000G](#) [HA0500500000G](#) [HA1000500000G](#) [HA1900500000G](#)
[HA0700500000G](#) [HA2200500000G](#) [HA0800500000G](#) [HA1800500000G](#) [HA1500500000G](#) [HA1700500000G](#)
[HA1100500000G](#) [HA2000500000G](#) [HA2300500000G](#)