


FOR REFERENCE ONLY

SPECIFICATIONS:

AC RATING: 10 AMPS @115VAC (RESISTIVE LOAD)
5 AMPS @115VAC (INDUCTIVE LOAD)
3 AMPS @115VAC (LAMP LOAD)
DC RATING: 10 AMPS @28VDC (RESISTIVE LOAD)
5 AMPS @28VDC (INDUCTIVE LOAD)
3 AMPS @28VDC (LAMP LOAD)
TYPE 7 CONTACT ARRANGEMENTS:
1/2 AMPERAGE LOADS SHOWN ABOVE
MECHANICAL LIFE: 500,000 CYCLES
ACTION: MOMENTARY SNAP OR PUSH PULL
OPERATING FORCE:
SERIES 20 & 30: 3 TO 5 POUNDS MOMENTARY
1/2 TO 2 POUNDS PUSH-PULL
SERIES 22 & 32: 2 TO 3 POUNDS MOMENTARY
WEIGHT: .050 POUNDS MAXIMUM
CASE: ALUMINUM ALLOY 2011-T3,
CLEAR ANODIZED IAW MIL-A-8625
PLUNGER: GLASS FILLED NYLON
BODY: DIALYL PHTHALATE IAW MIL-M-14
TERMINALS: THREADED #2-56 NC-2B

B NX201CB2B-XX



DESCRIPTION

"SERIES 20" MOMENTARY SWITCH
CONTACTS SPNO - SINGLE POLE NORMALLY OPEN
ADAPTER TYPE "C", COLOR BLACK
BUTTON #2, COLOR BLACK

ORDERING INFORMATION:

NX201CB2B-00	SWITCH ONLY
NX201CB2B-60	SWITCH, MOUNTING HARDWARE
NX201CB2B-61	SWITCH, MOUNTING HARDWARE, TERNIMAL HARDWARE
NX201CB2B-00EU	SWITCH ONLY (ROHS)
NX201CB2B-60EU	SWITCH, MOUNTING HARDWARE (ROHS)
NX201CB2B-61EU	SWITCH, MOUNTING HARDWARE, TERNIMAL HARDWARE (ROHS)

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

DWN. BY EWT		DATE 06/05/08		MATERIAL N/A	
CHECKED BY		DATE		FINISH N/A	
APPR. BY		DATE		WEIGHT — SCALE N/A	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON .XX .XXX ANGLES — ±.003 ±.5°				TITLE SWITCH SPNO MOMENTARY	
				DO NOT SCALE DWG. SHEET 1 OF 1	
				NEXUS STAMFORD, CONN	
				SIZE B	DWG. NO. NX201CB2B-XX

LET.	REVISION	CN #	DATE	CHK.
------	----------	------	------	------



SW-200-23
TERMINAL
(2)




SW-200-25
#2 LOCKWASHER
(2)




SW-200-72
#2-56 SCREW
(2)

TERMINAL
HARDWARE



SW-200-34
5/8-24 NUT
(1)



SW-200-35
5/8 LOCKWASHER
(1)

MOUNTING
HARDWARE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[NX201CB2B-61](#) [NX201CB2B](#) [NX201CB2B-60](#)