




ITEM #	PART #	QTY	DESCRIPTION	MATERIAL
1	AP-145-1M	1	SHELL ASS'Y	303 STAINLESS STEEL
2	AP-145-6	1	INSERT ASS'Y	DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS
3	AP-105-5	1	STRAIN RELIEF	NYLON
4	AP-116-3	1	WASHER	RUBBER
5	AP-136-8	1	NUT ADAPTER	BRASS, BLACK CHROME
6	AP-136-6	1	CLAMP SHIELD, OUTER	NICKEL PLATED BRASS
7	AP-136-5	1	CLAMP SHIELD INNER	NICKEL PLATED BRASS
8	SEE TABLE #1	1	BUSHING	RUBBER
9	SEE TABLE #1	1	WASHER	STAINLESS STEEL
10	SEE TABLE #1	1	SPRING	302 STAINLESS STEEL
11	AP-116-6	1	STUD	ANODIZED ALUMINUM ALLOY

NOTES:
1) UNLESS OTHERWISE SPECIFIED, CONNECTOR MEETS ALL
GENERAL REQUIREMENTS & SPECIFICATIONS OF MIL-C-55116

C AP-145MS-CP

TABLE #1				
AUDIO PLUG #	CABLE Ø	BUSHING	WASHER	SPRING
AP-145MS-1	Ø .165± .010	AP-116-17	AP-116-2	AP-116-4
AP-145MS-2	Ø .228± .010	AP-116-18	AP-116-2	AP-116-4
AP-145MS	Ø .250± .010	AP-116-8	AP-116-2	AP-116-4
AP-145MS-4	Ø .290± .010	AP-116-19	AP-116-2	AP-116-4
AP-145MS-5	Ø .320± .010	AP-116-20	AP-116-22	AP-116-21



SECTION Z-Z

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

						DWN.BY	HR	DATE	4/25/13	MATERIAL					
						CHECKED BY		DATE		FINISH					
						APPR.BY		DATE		WEIGHT	SCALE = 1.00 :1		NEXUS STAMFORD,CONN		
C	DEL: 9° ; 33° , ADD: 12° ; 36° ; TABLE #1, CHG: 45° TO 45° REF	226	8/26 2015	HR						TITLE					
B	CHG: ITEM #5 MAT'L	202	6/9 2014	HR		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES & OR (mm)				AUDIO PLUG		SIZE C		DWG. NO. AP-145MS-CP	
A	NEW RELEASE	173	4/25 2013	HR		TOLERANCES: DECIMAL: ±.XX(X.X) ±.XXX(X.XX) ±.000(X.000) ±.0X(0.X) ±.00X(0.0X) ±.000X(0.000)									
LET.	REVISION	CN #	DATE	CHK		FRACTION: ±X/XX ± X/XX ANGLES: ±X° ±X°				DO NOT SCALE DWG.		SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AP-145MS](#)