


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION


ALTW
CONFIDENTIAL
2015-11-19
R&D DEPT.

ALTW
DCC. DEPT.
CONFIDENTIAL
2016.06.13
ISSUED



Note:
* $\varnothing$ Important Dimension To Check.
* Electrical:
Impedance: 50 Ω
Frequency: 6GHz
V.S.W.R: 1.35 (max)
Insulator Resistance: 5000(min)
* Mechanical & Environmental:
Mating: 5/8"-24UNEF
Coupling Nut Retention: 100 lbs(min)
Cable Retention: 40 lbs(min)
Temperature Range: -40 $^{\circ}$ c~105 $^{\circ}$ c
Waterproof Rating: IP68
Salt Spary Corrosion Test: 48H

*Material:
Shell: Brass, Nickel Plated
Connector Body: Brass, Nickel Plated
Center Contact: Brass, Gold Plated
Insulator: PTFE
Crimp Ferrule: Brass, Nickel Plated
Gasket: Silicone, Red
*Cable Assembly:
Crimped Ferrule Size: HEX.213"
Crimped Pin Size: HEX.068"
Cable OD : $\varnothing$ 4.9~5.4mm



Recommend Cable
Stripping DIM'S

UNIT:mm		TITLE RF,N,ASSY SCREW,M CONN M PIN		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO RF5A-JMMCL8-00A2001	DRAWN BY Kaven	DATE 2015/11/19
TOLERANCE .X $\pm$ 0.25 .XX $\pm$ 0.1 .XXX $\pm$ 0.05 ANGLES $\pm$ 1 $^{\circ}$		SCALE 2:1	SIZE A4	SHEET 1 OF 1	DWG NO RF5A-JMMCL8-00A2001	CHECKED BY Doreen	DATE 2015/11/19	DATE 2015/11/19
REV. A		WC-REV. .0	$\varnothing$ Inspection item		CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015/11/19	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RF5A-JMMCL8-00A2001](#)