


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1650706~07	2016-04-16	Spring	Add ground pin





Cable ②

CC-03AFMM-QL8W00 ①

Conn.

White Printing
白色印刷



CC-03AFMM-QL8EXX

XX: 01~99Meters
01: 01Meter
02: 02Meters
...
99: 99Meters

- Note:
- * ① Important Dimension To Check.
 - * Working Voltage Rating: 300V AC
 - * Working Current Rating: Max. 20A
 - * Waterproof Rate: IP68.(Mated)
in 1 meter water within 24 hours
 - * Connector: Nylon+GF, Black.
 - * Pin: Copper Alloy, Glod & Ni Plated.
 - * Lock Nut: Nylon+GF, Black.
 - * Cable: SJTW 12WG*3C, Black,
PVC Jacket, OD=11.7mm.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

3	White	白
2	Green	綠
1	Black	黑
Conn.	Wire Color	
	Pin Out	

UNIT:mm	
TOLERANCE	±0.5

TITLE X Lok C-Size Cable 3 Pin 20A F Conn. M Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. B	WC-REV. A.1	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Spring	DATE 2016-04-16
DWG NO CC-03AFMM-QL8EXX	CHECKED BY Fisher	DATE 2016-04-16
CUSTOMER ALTW	APPROVED BY Kevin	DATE 2016-04-16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CC-03AFMM-QL8E01](#)