



3	White	白
2	Green	緑
1	Black	黒
Conn.	Wire Color	
Pin Out		

```

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

```

- *  Important Dimension To Check.
- * Working Voltage Rating: AC 300V
- * Working Current Rating: 20A
- * Waterproof Rate: IP68(Mated)
in 1 meter water within 24 hours
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold & Ni Plated
- * Cable: SJTW 12AWG*3C, Black
PVC Jacket, OD=11.7mm.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT : mm		
TOLERANCE		
.X	±0.25	
.XX	±0.1	
.XXX	±0.05	
ANGLES	±°	

TITLE			
X-Lok C-Size Cable 3 Pin 20A M Conn. M Pin			
SCALE	1:1	SIZE	A4
REV.	B	SHEET	1 OF 1
		WC-REV.	A.3
QC: Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Spring	2016-04-16
DWG NO	CHECKED BY	DATE
CC-03AMMM-QL8EXX	Fisher	2016-04-16
CUSTOMER	APPROVED BY	DATE
ALTW	Kevin	2016-04-16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CC-03AMMM-QL8E01](#)