


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION




ALTW
CONFIDENTIAL
2016-04-29
R&D DEPT.

DD-14AFMM-QR8D XX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters

Cable Length(L): 01~99Meters



7	Blue	藍	14	Brown/White	棕/白
6	Green	綠	13	Black/White	黑/白
5	Yellow	黃	12	Light Green	淡綠
4	Orange	橙	11	Pink	粉紅
3	Red	紅	10	White	白
2	Brown	棕	9	Gray	灰
1	Black	黑	8	Purple	紫
Conn.		Wire Color	Conn.		Wire Color
Pin Out			Pin Out		

Note:

- * ØØ Important Dimension To Check.
- * Working Voltage Rating: AC 300 V
- * Working Current Rating: 5A
- * Flame Class: UL94V-0 (UV Resistance)
- * Waterproof Rate: IP68(Mated)
In 1 meter water within 24 hours
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Cable: UL21388 20AWG*14C+AL.Mylar
Black, PVC Jacket UV Resistant, OD=8.5
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TOLERANCE ±0.5		TITLE X-Lok D Size Cable Molding 14Pin F Connector M Pin(05A)		SCALE 1:1		SIZE A4		SHEET 1 OF 1		REV. A		WC-REV. A.1		QC: Inspection item		ITEM NO		DRAWN BY Wes Fan		DATE 2016-04-29	
																		DWG NO DD-14AFMM-QR8DXX		CHECKED BY Spring Liu		DATE 2016-04-29	
																		CUSTOMER ALTW		APPROVED BY Kevin Hu		DATE 2016-04-29	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DD-14AFMM-QR8D01](#)